

The Pulsatron Series T7 was designed to feed chemical products on a timed schedule. Typical applications include the feed of biocides in open-air

cooling towers. The feed cycle is initiated and controlled by the programmable timer. The Series T7 provides everything you need in one unique, compact package to create a simple and cost effective metering system for timed applications.

A 7-day programmable timer controls the Series T7. The timer is programmable in 1-minute increments with up to 8 on/off cycles per day. Each timed event can be set to run any day of the week on a 7-day cycle.

Other control features include a standby mode, continuous 'ON' mode and the ability to adjust the stroke length from 0 to 100%.

Four distinct models are available, having pressure capabilities to 100 PSIG (7.0 BAR) @ 12 GPD (1.9 lph), and flow capabilities to 48 GPD (7.6 lph) @ 50 PSIG (3.3 BAR), with a turndown ratio of 10:1. Metering performance is reproducible to within  $\pm$  3% of maximum capacity.

#### Features

- Complete Timer Control in one unique package.
- Solid State 7 Day Electronic Timer.
- Isolated from Earth Ground.
- Few Moving Parts and Wall Mountable.
- Safe & Easy Priming with durable leak-free bleed valve assembly (standard).

## Controls



#### 7 Day Programmable Timer

- Program up to 8 On/Off Events Per Day
- Timed Events Can Be Set To Run Any Day Of The Week In A 7-Day Cycle.

**Manual Stroke Length** 

Turn-Down Ratio 10:1

## **Operating Benefits**

- Reliable metering performance.
- Rated "hot" for continuous duty.
- Leak-free, sealless, liquid end.



#### Aftermarket

- KOPkits
- Gauges
- Dampeners
  - Pressure Relief Valves
- Tanks
- Pre-Engineered Systems
- Process Controllers (MicroVision)



# **PULSAtion**<sup>®</sup> Series T7 Electronic Metering Pumps



#### **C**7t Series T7 **Specifications and Model Selection**

MODEL		LC13BA	LC14BA	LC64BA	LC44BA	
Capacity	GPH	0.50	1.00	1.25	2.00	
nominal	GPD	12	24	30	48	
(max.)	LPH	1.9	3.8	4.7	7.6	
Pressure	PSIG	100	100	100	50	
(max.)	BAR	7	7	7	3.3	
Connections:	Tubing	1/4" ID X 3/8" OD				

# **Engineering Data**

Pump Head Materials Available:

	PVC
	PVDF
	316 SS
Diaphragm:	PTFE-faced CSPE-backed
Check Valves Materials Available:	
Seats/O-Rings:	PTFE
-	CSPE
	Viton
Balls:	Ceramic
	PTFE
	316 SS
	Alloy C
Fittings Materials Available:	GFPPL
-	PVC
	PVDF
Bleed Valve:	Same as fitting and check valve
	selected, except 316SS
Injection Valve & Foot Valve Assy:	Same as fitting and check valve
	selected
Tubing:	Clear PVC
	White PE

GFPPL

#### Important: Material Code - GFPPL=Glass-filled Polypropylene, PVC=Polyvinyl Chloride, PE=Polyethylene, PVDF=Polyvinylidene Fluoride, CSPE=Generic formulation of Hypalon, a registered trademark of E.I. DuPont Company. Viton is a registered trademark of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

### **Engineering Data**

**Reproducibility:** Stroke Length Turn-Down Ratio: **Power Input:** 

Average Current Draw: @ 115 VAC; Amps: @ 230 VAC; Amps:

e

e

+/- 3% at maximum capacity 10:1 115 VAC/50-60 HZ/1 ph 230 VAC/50-60 HZ/1 ph

0.6 Amps 0.3 Amps @ 230 VAC

## **Custom Engineered Designs – Pre-Engineered Systems**



#### **Pre-Engineered Systems**

Pulsafeeder's Pre-Engineered Systems are designed to provide complete chemical feed solutions for all electronic metering applications. From stand alone simplex pH control applications to full-featured, redundant sodium hypochlorite disinfection metering, these rugged fabricated assemblies offer turn-key simplicity and industrial-grade durability. The UVstabilized, high-grade HDPE frame offers maximum chemical compatibility and structural rigidity. Each system is factory assembled and hydrostatically tested prior to shipment.

## **Dimensions**

Series T7 Dimensions (inches							
						Shipping	
Model No.	Α	В	С	D	E	Weight (lbs.)	
LC13BA	5.0	9.6	9.5	6.5	8.2	10	
LC14BA	5.0	9.9	9.5	6.5	8.5	10	
LC64BA	5.0	9.9	9.5	6.5	8.5	10	
LC44BA	5.4	10.6	11.3	7.4	9.2	11.8	
LC44BA	5.4		<u>  11.3</u>	7.4	9.2	11.8	

NOTE: Inches X 2.54 = cm

SHARRY Machinery (Shanghai) Co., Ltd 谐芮机械 (上海)有限公司 Tel: 021- 6488 1886 Fax: 021- 5186 2316 E-Mail:sharry@sharry-sh.com Web:www.sharry-sh.com SHARRY Machinery (Shanghai) Co.,Ltd

